

Honeywell**Pair of gloves Perfect Poly® Skin, Glove size: 9****Order data**

Order number	094250 9
GTIN	3603835501376
Item class	09A

Description**Version:**

Perfect Poly® Skin. Extremely touch-sensitive and close-fitting gloves with good grip, high comfort and resistance. **Silicone-free.**

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

silicone-free	yes
Touch sensitivity	very good
Heat protection	not available
Glove size	9
Oil grip	medium
DMF-free	no

Material of coating	PU
Manufacturer's designation	Perfect Poly Skin
Wet grip	medium
Breathability	very good
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	10
Glove characteristics	Silicone-free
Glove characteristics	Suitable for allergy sufferers
EN 388	3111X
Backing material	Polyamide
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	220 - 260 mm
Colour	grey / blue
Weight	14-20 g
Knitted technology	15G
Application	reusable
Cut protection class	1
Type of product	Multi-purpose gloves