

Garant
Screw-on toolholder, right-hand, Shank / insert size: 12/11 mm

Order data

Order number	261108 12/11
GTIN	4045197929105
Item class	21T

Technical description

Shank size	12 mm
suitable indexable insert	VB.. 1103..
Pack of insert screws	269028 22
Functional width L ₄	16 mm
Head length L ₁	21.5 mm
Insert size	11 mm
ISO code toolholder	SVJBR/L 1212F11
Overall length L	80 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500