

Garant
Screw-on toolholder, right-hand, Shank / insert size: 10/06mm

Order data

Order number	260000 10/06
GTIN	4045197929136
Item class	21T

Technical description

Overall length L	70 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Shank size	10 mm
ISO code toolholder	SCSCR/L 1010E06
Functional width L ₄	12 mm
Head length L ₁	12 mm
Pack of insert screws	269028 22
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500