

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 16/09mm**

**Order data**

Order number	260000 16/09
GTIN	4045197929150
Item class	21T

**Technical description**

ISO code toolholder	SCSCR/L 1616H09
Functional width L <sub>4</sub>	20 mm
Head length L <sub>1</sub>	20 mm
Insert size	9 mm
Pack of insert screws	269028 2
suitable indexable insert	CC.. 09T3..
Shim	269005 1
Overall length L	101 mm
Shank size	16 mm
Shim screw	269013 2
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 2	269028 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500