

Garant**Screw-on toolholder, right-hand, Shank / insert size: 25/12mm****Order data**

Order number	260000 25/12
GTIN	4045197929198
Item class	21T

Technical description

ISO code toolholder	SCSCR/L 2525M12
Shim	269005 6
suitable indexable insert	CC.. 1204..
Shank size	25 mm
Functional width L ₄	32 mm
Shim screw	269013 5
Pack of insert screws	269028 20
Head length L ₁	27 mm
Insert size	12 mm
Overall length L	151 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500