

**Garant**
**Scrw-on toolholder, left-hand, Shank / insert size: 8/06mm**

**Order data**

Order number	260001 8/06
GTIN	4045197929204
Item class	21T

**Technical description**

Pack of insert screws	269028 22
Functional width $L_4$	10 mm
Overall length $L$	60 mm
ISO code toolholder	SCSCR/L 0808D06
Head length $L_1$	12 mm
suitable indexable insert	CC.. 0602..
Shank size	8 mm
Insert size	6 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500