

**Garant****Scrw-on toolholder, left-hand, Shank / insert size: 12/09mm****Order data**

Order number	260001 12/09
GTIN	4045197929242
Item class	21T

**Technical description**

Shank size	12 mm
ISO code toolholder	SCSCR/L 1212F09
Head length L <sub>1</sub>	19 mm
Pack of insert screws	269028 2
Functional width L <sub>4</sub>	16 mm
Overall length L	80 mm
suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 2	269028 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500