

Garant
Scrw-on toolholder, left-hand, Shank / insert size: 10/06mm

Order data

Order number	260001 10/06
GTIN	4045197929235
Item class	21T

Technical description

Insert size	6 mm
suitable indexable insert	CC.. 0602..
Shank size	10 mm
Pack of insert screws	269028 22
Overall length L	70 mm
ISO code toolholder	SCSCR/L 1010E06
Head length L ₁	12 mm
Functional width L ₄	12 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500