

**Copper pipe bending pliers, for pipe outer Ø: 10 mm****Order data**

Order number	821300 10
GTIN	3521742511106
Item class	86B

Description**Version:**

For bending angles up to 180° with smallest possible radius and no deformation of the pipe.
Forming segment with graduations.
Strong design, forged from steel; cadmium plated.

Application:

For bending soft copper pipes. Reverse curves can be bent in all directions, without transitions or shoulders, because the pliers can also be set in the middle of the pipe.
Bending radius (centre of pipe): 23 mm

Technical description

Bending radius (centre of pipe)	23 mm
for pipe outer Ø	10 mm
Type of product	Bending machine