

**Garant****Scrw-on toolholder, left-hand, Shank / insert size: 25/12mm****Order data**

Order number	260001 25/12
GTIN	4045197929303
Item class	21T

**Technical description**

Pack of insert screws	269028 20
ISO code toolholder	SCSCR/L 2525M12
Head length L <sub>1</sub>	27 mm
Shim	269005 6
Insert size	12 mm
Shim screw	269013 5
Functional width L <sub>4</sub>	32 mm
Overall length L	151 mm
Shank size	25 mm
suitable indexable insert	CC.. 1204..
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

### Accessories

Set of insert screws Type 2	269028 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500

---