



Pair of gloves HyFlex® 11-619, Glove size: 10



Order data

Order number	094262 10
GTIN	10076490481114
Item class	04P

Description

Version:

HyFlex® series. Extremely thin and yet robust gloves of **18-gauge** knitted fabric. Particularly suitable for light assembly work with high demands on precision, final assembly of electric motors, air conditioning systems, wiring harnesses.

HyFlex® 11-619. With coating out to the pulse area.

Standard:

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Knitted technology: 18G

Colour: white

Technical description

Weight	7.4 g
Touch sensitivity	very good
Material of coating	PU

Glove size	10
Heat protection	not available
Wet grip	medium
Accuracy of fit	very good
DMF-free	no
Oil grip	good
silicone-free	no
Breathability	very good
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
EN 388:2016	2121X
Backing material	Nylon
Coating	PU
Application range	Precision
Colour	white
Knitted technology	18G
Type of product	Multi-purpose gloves