

**Ansell****Pair of gloves HyFlex® 11-600, Glove size: 10****Order data**

Order number	094240 10
GTIN	10076490499317
Item class	04P

**Description****Version:**

HyFlex® 11-600. Fine knitted gloves with palm coating for dry working conditions. For precision work, highly breathable. With a thin layer of backing material for use in industry and light and fine work for which **maximum freedom of movement** is required. Protects the product against fingerprints, residues from the gloves themselves and general dirt. Particularly suitable for the assembly of small components such as ball bearings, joints and springs.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

DMF-free	no
Glove size	10
Accuracy of fit	very good
Wet grip	medium

Oil grip	medium
Touch sensitivity	very good
Material of coating	PU
silicone-free	no
Heat protection	not available
Breathability	very good
Series	HyFlex®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
EN 388	3121A
Backing material	Nylon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	200 mm
Colour	white
Weight	11,6 g
Knitted technology	15G
Application	reusable
Material	PU
Cut protection class	A
Type of product	Multi-purpose gloves