



Pair of gloves HyFlex® 11-618, Glove size: 7



Order data

Order number	094260 7
GTIN	10076490489479
Item class	04P

Description

Version:

HyFlex® 11-618. Lightweight glove with a very good combination of cut protection, oil repellence and increased durability. Extremely thin and yet robust gloves of **18-gauge** knitted fabric. Particularly suitable for light assembly work with high demands on precision, final assembly of electric motors, air conditioning systems, wiring harnesses.

Version of the advertising text:

Thin fine knitted gloves for light assembly work where high precision is required.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Accuracy of fit	very good
Breathability	very good
silicone-free	no

Heat protection	not available
Oil grip	good
Touch sensitivity	very good
DMF-free	no
Wet grip	medium
Material of coating	PU
Glove size	7
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12
Glove characteristics	Suitable for allergy sufferers
EN 388	3121X
Backing material	Nylon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	195 mm
Colour	black / blue
Weight	7,4 g
Knitted technology	18G
Application	reusable
Material	PU
Cut protection class	FG
Type of product	Multi-purpose gloves