

Garant**Trolley with handle T1, Type: T14****Order data**

Order number	918500 T14
GTIN	4045197612014
Item class	91T

Description**Version:**

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene.

2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Perforated panel No. 918580 size SP1. Not supplied.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Weight	27 kg
Height of top shelf	853 mm

Platform area width	609 mm
Safe working load	200 kg
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Height of bottom shelf	195 mm
Wheel Ø	125 mm
Height	1019 mm
Standard	EN 1757-3
Type	T14
Material of wheel	Polyurethane tyres
Width	813 mm
Platform area depth	459 mm
Depth	459 mm
Type of product	Trolley with handle

Accessories

Perforated panel for bolting in Type SP1	918580 SP1
Clipboard for table trolleys	918581