

**Garant****Platform trolley T3, Type: T32****Order data**

Order number	918520 T32
GTIN	4045197611888
Item class	91T

**Description****Version:**

1 Platform area.

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene. 2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Perforated panel No. 918580. Not supplied.

**Colour:**

Silver **powder-coated.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Height: 915 mm

Width: 970 mm

Depth: 509 mm

Platform area width: 850 mm

Platform area depth: 500 mm

Platform area height: 195 mm

## Technical description

Wheel Ø	125 mm
Width	970 mm
Height	915 mm
Material of wheel	Polyurethane tyres
Weight	20 kg
Type	T32
Safe working load	250 kg
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Standard	EN 1757-3
Platform area width	850 mm
Platform area height	195 mm
Depth	509 mm
Platform area depth	500 mm
Type of product	Platform trolley

## Accessories

Clipboard for table trolleys	918581
Perforated panel for bolting in Type SP2	918580 SP2