

Garant**Platform trolley T3, Type: T32****Order data**

Order number	918520 T32
GTIN	4045197611888
Item class	91T

Description**Version:**

1 Platform area.

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene. 2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Perforated panel No. 918580. Not supplied.

Colour:

Silver **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	125 mm
---------	--------

Width	970 mm
Height	915 mm
Material of wheel	Polyurethane tyres
Weight	20 kg
Type	T32
Safe working load	250 kg
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Standard	EN 1757-3
Platform area width	850 mm
Platform area height	195 mm
Depth	509 mm
Platform area depth	500 mm
Type of product	Platform trolley

Accessories

Clipboard for table trolleys	918581
Perforated panel for bolting in Type SP2	918580 SP2