

Garant**Table trolley T9, Type: T94****Order data**

Order number	918550 T94
GTIN	4045197612137
Item class	91T

Description**Version:**

2 shelves.

Middle shelf available as an accessory. Platform made of **chipboard** with anthracite-coloured scratch-resistant surface.

Welded steel design.

Handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Intermediate shelf No. 918575; perforated panel No. 918580. Not supplied.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

maximum load capacity	500 kg
-----------------------	--------

Height	925 mm
Type	T94
Platform area width	1000 mm
Width	1190 mm
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Material of wheel	Polyurethane tyres
Standard	EN 1757-3
Height of top shelf	925 mm
Load capacity of top shelf	200 kg
Wheel Ø	200 mm
Platform area depth	600 mm
Depth	609 mm
Height of bottom shelf	270 mm
Weight	49 kg
Type of product	Table trolleys

Accessories

Intermediate shelf for bolting into table trolley T9 Platform area depth 600 mm	918575 600
Perforated panel for bolting in Type SP4	918580 SP4
Clipboard for table trolleys	918581