

**Garant****Platform trolley T3, Type: T34****Order data**

Order number	918520 T34
GTIN	4045197611895
Item class	91T

**Description****Version:**

1 Platform area.

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene. 2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Perforated panel No. 918580. Not supplied.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Safe working load	500 kg
-------------------	--------

Platform area width	1000 mm
Platform area height	270 mm
Weight	34.4 kg
Wheel Ø	200 mm
Height	990 mm
Number of fixed wheels without parking brake	2
Material of wheel	Polyurethane tyres
Width	1120 mm
Standard	EN 1757-3
Number of castors with parking brake	2
Type	T34
Depth	609 mm
Platform area depth	600 mm
Type of product	Platform trolley

---

## Accessories

Clipboard for table trolleys	918581
Perforated panel for bolting in Type SP4	918580 SP4