

Garant**Table trolley T9, Type: T96****Order data**

| | |
|--------------|---------------|
| Order number | 918550 T96 |
| GTIN | 4045197612144 |
| Item class | 91T |

Description**Version:**

2 shelves.

Middle shelf available as an accessory. Platform made of **chipboard** with anthracite-coloured scratch-resistant surface.

Welded steel design.

Handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Intermediate shelf No. 918575; perforated panel No. 918580. Not supplied.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|----------|-----------|
| Standard | EN 1757-3 |
|----------|-----------|

| | |
|--|--------------------|
| Number of castors with parking brake | 2 |
| Platform area depth | 700 mm |
| Platform area width | 1000 mm |
| Wheel Ø | 200 mm |
| maximum load capacity | 500 kg |
| Depth | 709 mm |
| Height | 925 mm |
| Height of top shelf | 925 mm |
| Weight | 54 kg |
| Height of bottom shelf | 270 mm |
| Type | T96 |
| Material of wheel | Polyurethane tyres |
| Load capacity of top shelf | 200 kg |
| Width | 1190 mm |
| Number of fixed wheels without parking brake | 2 |
| Type of product | Table trolleys |

Accessories

| | |
|---|------------|
| Clipboard for table trolleys | 918581 |
| Perforated panel for bolting in Type SP5 | 918580 SP5 |
| Intermediate shelf for bolting into table trolley T9 Platform area depth 700 mm | 918575 700 |