

**Garant****Platform trolley T3, Type: T36****Order data**

Order number	918520 T36
GTIN	4045197612106
Item class	91T

**Description****Version:**

1 Platform area.

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene. 2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Perforated panel No. 918580. Not supplied.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Standard	EN 1757-3
----------	-----------

Platform area width	1000 mm
Type	T36
Weight	34 kg
Number of fixed wheels without parking brake	2
Safe working load	500 kg
Platform area height	270 mm
Material of wheel	Polyurethane tyres
Width	1120 mm
Height	990 mm
Number of castors with parking brake	2
Wheel Ø	200 mm
Depth	709 mm
Platform area depth	700 mm
Type of product	Platform trolley

---

## Accessories

Clipboard for table trolleys	918581
Perforated panel for bolting in Type SP5	918580 SP5