

**Garant****Table trolley T9, Type: T98****Order data**

Order number	918550 T98
GTIN	4045197612151
Item class	91T

**Description****Version:**

2 shelves.

Middle shelf available as an accessory. Platform made of **chipboard** with anthracite-coloured scratch-resistant surface.

Welded steel design.

Handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Intermediate shelf No. 918575; perforated panel No. 918580. Not supplied.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Material of wheel	Polyurethane tyres
-------------------	--------------------

Standard	EN 1757-3
Wheel Ø	200 mm
Type	T98
Height	925 mm
Load capacity of top shelf	200 kg
maximum load capacity	500 kg
Height of top shelf	925 mm
Number of castors with parking brake	2
Depth	809 mm
Platform area width	1200 mm
Height of bottom shelf	270 mm
Number of fixed wheels without parking brake	2
Width	1390 mm
Platform area depth	800 mm
Weight	64 kg
Type of product	Table trolleys

---

## Accessories

Clipboard for table trolleys	918581
Intermediate shelf for bolting into table trolley T9 Platform area depth 800 mm	918575 800
Perforated panel for bolting in Type SP6	918580 SP6