

Garant**Platform trolley TS9 with 4 shelves, Type: TS94****Order data**

Order number	918560 TS94
GTIN	4045197684448
Item class	91T

Description**Version:**

Welded steel construction, shelves of **chipboard** with anthracite-coloured scratch-resistant surface. Adjustable at 130 mm intervals. Side-mounted handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Additional shelf No. 918577. Perforated panel No. 918580.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Total load capacity	500 kg
---------------------	--------

Weight	70 kg
Wheel Ø	200 mm
Load capacity of each loose shelf	75 kg
Platform area width	1000 mm
Width	1225 mm
Standard	EN 1757-3
Push handle	yes
Height	1835 mm
Material of wheel	Solid rubber
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Type	TS94
Height adjustment interval	130 mm
Depth	610 mm
Platform area depth	600 mm
Height adjustment interval	130 mm
Type of product	Platform trolley

Accessories

Perforated panel for bolting in Type SP4	918580 SP4
Clipboard for table trolleys	918581
Intermediate shelf for platform trolley TS9 for bolting in Platform area depth 600 mm	918577 600