

**Garant****Table trolley T5, Type: T54****Order data**

Order number	918530 T54
GTIN	4045197611840
Item class	91T

**Description****Version:**

2 shelves.

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene.

2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

**Standard:****EN 1757-3****Optional extras:**

Intermediate shelf No. 918570; perforated panel No. 918580. Not supplied.

**Colour:**Silver **powder-coated**.**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Platform area width	850 mm
---------------------	--------

Number of castors with parking brake	2
Height of top shelf	850 mm
Platform area depth	500 mm
Load capacity of top shelf	80 kg
Wheel Ø	125 mm
Number of fixed wheels without parking brake	2
Height	1020 mm
Material of wheel	Polyurethane tyres
Depth	509 mm
Type	T54
Width	980 mm
Weight	34 kg
maximum load capacity	250 kg
Standard	EN 1757-3
Height of bottom shelf	195 mm
Type of product	Table trolleys

## Accessories

Clipboard for table trolleys	918581
Perforated panel for bolting in Type SP2	918580 SP2
Additional drawer for table trolley Type 75	918556 75
Intermediate shelf for bolting into table trolleys T5 and T7 Platform area depth 500 mm	918570 500