

**Garant****Platform trolley TS9 with 4 shelves, Type: TS96****Order data**

|              |               |
|--------------|---------------|
| Order number | 918560 TS96   |
| GTIN         | 4045197684455 |
| Item class   | 91T           |

**Description****Version:**

Welded steel construction, shelves of **chipboard** with anthracite-coloured scratch-resistant surface. Adjustable at 130 mm intervals. Side-mounted handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Additional shelf No. 918577. Perforated panel No. 918580.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

|       |         |
|-------|---------|
| Width | 1225 mm |
|-------|---------|

|                                              |                  |
|----------------------------------------------|------------------|
| Wheel Ø                                      | 200 mm           |
| Height                                       | 1835 mm          |
| Push handle                                  | yes              |
| Number of castors with parking brake         | 2                |
| Number of fixed wheels without parking brake | 2                |
| Platform area width                          | 1000 mm          |
| Standard                                     | EN 1757-3        |
| Load capacity of each loose shelf            | 85 kg            |
| Type                                         | TS96             |
| Total load capacity                          | 500 kg           |
| Material of wheel                            | Solid rubber     |
| Weight                                       | 76 kg            |
| Height adjustment interval                   | 130 mm           |
| Depth                                        | 710 mm           |
| Platform area depth                          | 700 mm           |
| Height adjustment interval                   | 130 mm           |
| Type of product                              | Platform trolley |

---

## Accessories

|                                                                                       |            |
|---------------------------------------------------------------------------------------|------------|
| Clipboard for table trolleys                                                          | 918581     |
| Intermediate shelf for platform trolley TS9 for bolting in Platform area depth 700 mm | 918577 700 |
| Perforated panel for bolting in Type SP5                                              | 918580 SP5 |