

**Garant****Table trolley T5, Type: T56****Order data**

Order number	918530 T56
GTIN	4045197611857
Item class	91T

**Description****Version:**

2 shelves.

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene.

2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Intermediate shelf No. 918570; perforated panel No. 918580. Not supplied.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Width	1130 mm
-------	---------

Platform area width	1000 mm
Depth	609 mm
Material of wheel	Polyurethane tyres
Weight	42 kg
Number of castors with parking brake	2
Standard	EN 1757-3
Type	T56
Wheel Ø	125 mm
Height of bottom shelf	195 mm
Height	1020 mm
Number of fixed wheels without parking brake	2
Height of top shelf	850 mm
Platform area depth	600 mm
Load capacity of top shelf	80 kg
maximum load capacity	250 kg
Type of product	Table trolleys

## Accessories

Perforated panel for bolting in Type SP3	918580 SP3
Clipboard for table trolleys	918581
Intermediate shelf for bolting into table trolleys T5 and T7 Platform area depth 600 mm	918570 600
Additional drawer for table trolley Type 75	918556 75