

**Garant****Platform trolley TS9 with 4 shelves, Type: TS98****Order data**

Order number	918560 TS98
GTIN	4045197684462
Item class	91T

**Description****Version:**

Welded steel construction, shelves of **chipboard** with anthracite-coloured scratch-resistant surface. Adjustable at 130 mm intervals. Side-mounted handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Optional extras:**

Additional shelf No. 918577. Perforated panel No. 918580.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Total load capacity	500 kg
---------------------	--------

Wheel Ø	200 mm
Weight	91 kg
Width	1390 mm
Standard	EN 1757-3
Platform area width	1200 mm
Load capacity of each loose shelf	95 kg
Height	1835 mm
Push handle	yes
Number of castors with parking brake	2
Material of wheel	Solid rubber
Type	TS98
Number of fixed wheels without parking brake	2
Height adjustment interval	130 mm
Depth	810 mm
Platform area depth	800 mm
Height adjustment interval	130 mm
Type of product	Platform trolley

---

## Accessories

Clipboard for table trolleys	918581
Intermediate shelf for platform trolley TS9 for bolting in Platform area depth 800 mm	918577 800
Perforated panel for bolting in Type SP6	918580 SP6