

Garant**Table trolley T7, Type: T76****Order data**

Order number	918540 T76
GTIN	4045197611871
Item class	91T

Description**Version:**

3 shelves.

Middle shelf can be set to 3 heights. Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene. 2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Perforated panel No. 918580. Not supplied.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Depth	609 mm
-------	--------

Height of middle shelf	522 mm
Height of top shelf	850 mm
Standard	EN 1757-3
Load capacity of middle shelf	80 kg
Wheel Ø	125 mm
Width	1130 mm
Number of castors with parking brake	2
Load capacity of top shelf	80 kg
maximum load capacity	250 kg
Type	T76
Material of wheel	Polyurethane tyres
Height	1020 mm
Number of fixed wheels without parking brake	2
Platform area depth	600 mm
Platform area width	1000 mm
Weight	58 kg
Height of bottom shelf	195 mm
Type of product	Table trolleys

Accessories

Additional drawer for table trolley Type 75	918556 75
Clipboard for table trolleys	918581
Perforated panel for bolting in Type SP3	918580 SP3
Intermediate shelf for bolting into table trolleys T5 and T7 Platform area depth 600 mm	918570 600