

**Platform trolley, Type: 2500****Order data**

Order number	919800 2500
GTIN	4017976025001
Item class	96F

Description**Version:**

Welded steel sections and tubes, platform made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Material of wheel	TPE
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Standard	EN 1757-3
Type	2500
Safe working load	500 kg

Height	948 mm
Weight	23 kg
Wheel Ø	160 mm
Platform area width	850 mm
Platform area height	228 mm
Width	975 mm
Depth	509 mm
Platform area depth	500 mm
Type of product	Platform trolley