

Garant**Table trolley T9, Type: T92****Order data**

Order number	918550 T92
GTIN	4045197612120
Item class	91T

Description**Version:**

2 shelves.

Middle shelf available as an accessory. Platform made of **chipboard** with anthracite-coloured scratch-resistant surface.

Welded steel design.

Handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Optional extras:

Intermediate shelf No. 918575; perforated panel No. 918580. Not supplied.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Type	T92
Height of bottom shelf	195 mm
Wheel Ø	125 mm
Material of wheel	Polyurethane tyres
Height	850 mm
Platform area width	850 mm
Depth	509 mm
maximum load capacity	250 kg
Platform area depth	500 mm
Number of fixed wheels without parking brake	2
Width	1040 mm
Load capacity of top shelf	200 kg
Height of top shelf	850 mm
Standard	EN 1757-3
Weight	33 kg
Number of castors with parking brake	2
Type of product	Table trolleys

Accessories

Additional drawer for table trolley Type 75	918556 75
Perforated panel for bolting in Type SP2	918580 SP2
Clipboard for table trolleys	918581
Intermediate shelf for bolting into table trolley T9 Platform area depth 500 mm	918575 500