

**Garant****Trolley with handle T1, Type: T12****Order data**

Order number	918500 T12
GTIN	4045197612007
Item class	91T

**Description****Version:**

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene.

2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

**Standard:**

**EN 1757-3**

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Type	T12
Weight	15 kg
Safe working load	250 kg

Height	900 mm
Number of castors with parking brake	2
Height of bottom shelf	195 mm
Standard	EN 1757-3
Width	860 mm
Platform area width	600 mm
Number of fixed wheels without parking brake	2
Wheel Ø	125 mm
Material of wheel	Polyurethane tyres
Platform area depth	500 mm
Depth	509 mm
Type of product	Trolley with handle