

Garant**Trolley with handle T1, Type: T12****Order data**

Order number	918500 T12
GTIN	4045197612007
Item class	91T

Description**Version:**

Welded steel construction, platform of **chipboard** with anthracite-coloured scratch-resistant surface.

Handle with Haptoprene® insert and impact resistant polypropylene.

2 fixed wheels and 2 castors (with brakes) with treadless polyurethane tyres and roller bearings.

Standard:

EN 1757-3

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Type	T12
Weight	15 kg
Safe working load	250 kg

Height	900 mm
Number of castors with parking brake	2
Height of bottom shelf	195 mm
Standard	EN 1757-3
Width	860 mm
Platform area width	600 mm
Number of fixed wheels without parking brake	2
Wheel Ø	125 mm
Material of wheel	Polyurethane tyres
Platform area depth	500 mm
Depth	509 mm
Type of product	Trolley with handle