

Garant**Short drill chuck Form AD, SK 40, Clamping range: 0,5-13mm****Order data**

Order number	301425 0,5-13
GTIN	4045197931771
Item class	31B

Description**Version:**

For clockwise and anticlockwise rotation.

With Balluff/RFID chip bore. Maximum radial run-out $\leq 20 \mu\text{m}$.

Sandblasted and ground.

- **slim design.**
- **targeted coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

Supplied with:

Torx® chuck key with T-handle **for high clamping force.**

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	0.5 - 13 mm
Overhang dimension A	76 mm
External \varnothing D	43 mm
Spare Torx® chuck key No. 625220	TX25
Type	slim
Adapter	SK 40
Arbor standard	ISO 7388-1

Shape	AD
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 20 \mu\text{m}$
maximum tightening torque $M_{d\text{max}}$	$\leq 14 \text{ Nm}$
Type of product	Short drill chuck