

Garant
Short drill chuck Form A, HSK-A 63, Clamping range: 0,3-8mm

Order data

Order number	307725 0,3-8
GTIN	4045197931863
Item class	31B

Description
Version:

- **For clockwise and anticlockwise rotation.**
- **With RFID/Balluffchip bore.**

With through coolant feed up to max. 50 bar.

Concentricity $\leq 20 \mu\text{m}$.

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Clamping range	0.3 - 8 mm
External \varnothing D	35 mm
Overhang dimension A	93 mm
Spare Torx® chuck key No. 625220	TX25
Type	slim
Adapter	HSK-A 63

Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 µm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck