

Garant
Short drill chuck Form A, HSK-A 100, Clamping range: 1-16mm

Order data

Order number	307735 1-16
GTIN	4045197931894
Item class	31B

Description
Version:

- **For clockwise and anticlockwise rotation.**
- **With RFID/Balluffchip bore.**

With through coolant feed up to max. 50 bar.

Concentricity $\leq 20 \mu\text{m}$.

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Spare Torx® chuck key No. 625220	TX25
External \varnothing D	50 mm
Overhang dimension A	110 mm
Clamping range	1 - 16 mm
Type	slim

Adapter	HSK-A 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 μm
Type of product	Short drill chuck