



## Table trolley with 2 platforms, Type: 2400



### Order data

Order number	919860 2400
GTIN	4017976024004
Item class	96F

### Description

**Version:**

Welded steel sections and tubes, platforms made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, and hubs with grooved ball bearings.

**Standard:**

EN 1757-3

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Weight	37 kg
Wheel Ø	160 mm
Height of bottom shelf	228 mm
Type	2400
Platform area depth	500 mm
Platform area width	850 mm

Load capacity of top shelf	200 kg
Material of wheel	TPE
maximum load capacity	500 kg
Depth	509 mm
Number of castors with parking brake	2
Height	860 mm
Height of top shelf	860 mm
Number of fixed wheels without parking brake	2
Width	1047 mm
Standard	EN 1757-3
Type of product	Table trolleys