



Table trolley with 2 platforms, Type: 2401



Order data

Order number	919860 2401
GTIN	4017976024011
Item class	96F

Description

Version:

Welded steel sections and tubes, platforms made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, and hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Load capacity of top shelf	200 kg
Standard	EN 1757-3
Platform area depth	600 mm
Platform area width	1000 mm
Number of castors with parking brake	2
Width	1197 mm

Height of top shelf	900 mm
Height	900 mm
Material of wheel	TPE
Wheel Ø	200 mm
Type	2401
Weight	44 kg
Height of bottom shelf	270 mm
Depth	609 mm
maximum load capacity	600 kg
Number of fixed wheels without parking brake	2
Type of product	Table trolleys