



Platform trolley with 4 platforms, Type: 8313



Order data

Order number	919880 8313
GTIN	4017976083131
Item class	96F

Description

Version:

Welded steel sections and tubes, end walls with vertical tube struts at 130 mm spacing. Platforms made of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	200 mm
Number of fixed wheels without parking brake	2
Height of shelf 3	1069 mm

Push handle	yes
Total load capacity	600 kg
Standard	EN 1757-3
Number of castors with parking brake	2
Height of shelf 4	1469 mm
Platform area width	1200 mm
Material of wheel	TPE
Weight	97 kg
Width	1369 mm
Type	8313
Height of shelf 1	269 mm
Height of shelf 2	669 mm
Load capacity of each loose shelf	90 kg
Height	1800 mm
Height adjustment interval	100 mm
Depth	809 mm
Platform area depth	800 mm
Height adjustment interval	100 mm
Type of product	Platform trolley