



## Table trolley with 2 platforms, Type: 2402



### Order data

Order number	919860 2402
GTIN	4017976024028
Item class	96F

### Description

**Version:**

Welded steel sections and tubes, platforms made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, and hubs with grooved ball bearings.

**Standard:**

EN 1757-3

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Wheel Ø	200 mm
Platform area width	1000 mm
Height	900 mm
Standard	EN 1757-3
Height of bottom shelf	270 mm
Height of top shelf	900 mm

Material of wheel	TPE
Load capacity of top shelf	200 kg
Depth	709 mm
Width	1197 mm
Type	2402
Platform area depth	700 mm
Weight	49 kg
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
maximum load capacity	600 kg
Type of product	Table trolleys