



Table trolley with 2 platforms, Type: 4842



Order data

Order number	919870 4842
GTIN	4017976348421
Item class	96F

Description

Version:

Welded steel construction, **oil-tight trays**.

2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Upper **oil-tight tray** with **150 mm** high edge.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Type	4842
Material of wheel	TPE
Weight	52 kg

Platform area width	1000 mm
Height of bottom shelf	248 mm
Height of top shelf	870 mm
Wheel Ø	200 mm
Width	1171 mm
Height	1020 mm
Load capacity of top shelf	200 kg
maximum load capacity	400 kg
Standard	EN 1757-3
Platform area depth	700 mm
Depth	700 mm
Type of product	Table trolleys