

**Table trolley with 2 platforms, Type: 2740****Order data**

Order number	919820 2740
GTIN	4017976027401
Item class	96F

Description**Version:**

Welded steel sections and tubes, platform made of chipboard with beech-effect finish, resting on an angle section steel frame, raised edge 12 mm high.

2 fixed wheels and 2 castors Ø 125 mm (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Platform area depth	500 mm
Type	2740
Standard	EN 1757-3
Height of top shelf	820 mm

Wheel Ø	125 mm
Height of bottom shelf	200 mm
Load capacity of top shelf	80 kg
Weight	28 kg
Platform area width	850 mm
Number of castors with parking brake	2
Depth	511 mm
Height	1040 mm
Width	985 mm
maximum load capacity	300 kg
Number of fixed wheels without parking brake	2
Type of product	Table trolleys