

**Table trolley with 2 platforms, Type: 2403****Order data**

Order number	919860 2403
GTIN	4017976024035
Item class	96F

Description**Version:**

Welded steel sections and tubes, platforms made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, and hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Material of wheel	TPE
Platform area depth	800 mm
Number of fixed wheels without parking brake	2
Wheel Ø	200 mm
Weight	58 kg
Width	1397 mm

Height	900 mm
Type	2403
Height of top shelf	900 mm
Height of bottom shelf	270 mm
Standard	EN 1757-3
Depth	809 mm
Number of castors with parking brake	2
Platform area width	1200 mm
Load capacity of top shelf	200 kg
maximum load capacity	600 kg
Type of product	Table trolleys