



Table trolley with 2 platforms up to 1200 kg, Type: 12403



Order data

Order number	919865 12403
GTIN	4017976124032
Item class	96F

Description

Version:

Welded steel and sections and tubes, platforms made of non-slip platform of marine plywood. 2 fixed wheels and 2 castors (with parking brake), high-grade resilient solid blue-grey rubber treadless tyres (200x50 mm), and hubs with roller bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height	925 mm
Material of wheel	Resilient solid rubber
Platform area width	1200 mm
Height of bottom shelf	283 mm
Number of fixed wheels without parking brake	2
Depth	800 mm

Standard	EN 1757-3
Load capacity of top shelf	500 kg
Platform area depth	800 mm
Type	12403
Height of top shelf	925 mm
Wheel Ø	200 mm
Width	1410 mm
maximum load capacity	1200 kg
Number of castors with parking brake	2
Weight	77 kg
Type of product	Table trolleys