



Table trolley with 2 platforms, Type: 2742



Order data

Order number	919820 2742
GTIN	4017976021300
Item class	96F

Description

Version:

Welded steel sections and tubes, platform made of chipboard with beech-effect finish, resting on an angle section steel frame, raised edge 12 mm high.

2 fixed wheels and 2 castors Ø 125 mm (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height of bottom shelf	200 mm
Height of top shelf	820 mm
Standard	EN 1757-3
Load capacity of top shelf	80 kg

maximum load capacity	300 kg
Wheel Ø	125 mm
Number of fixed wheels without parking brake	2
Weight	36 kg
Type	2742
Depth	611 mm
Number of castors with parking brake	2
Material of wheel	TPE
Platform area depth	600 mm
Platform area width	1000 mm
Height	1040 mm
Width	1135 mm
Type of product	Table trolleys