

**Table trolley with 3 platforms, Type: 4830****Order data**

Order number	919875 4830
GTIN	4017976048307
Item class	96F

**Description****Version:**

Welded steel construction, 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

**Oil-tight trays** with **40 mm** high edge, 3 shelves.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Type	4830
Material of wheel	TPE
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Height of bottom shelf	207 mm

Width	1021 mm
Load capacity of top shelf	200 kg
Height of top shelf	829 mm
maximum load capacity	400 kg
Load capacity of middle shelf	200 kg
Height	870 mm
Weight	46 kg
Wheel Ø	160 mm
Platform area width	850 mm
Height of middle shelf	519 mm
Standard	EN 1757-3
Platform area depth	500 mm
Depth	500 mm
Type of product	Table trolleys