

Ansell**Pair of gloves HyFlex® 11-801, Glove size: 10****Order data**

Order number	094351 10
GTIN	10076490491809
Item class	04P

Description**Version:**

HyFlex® series. Versatile gloves with nitrile foam coating for precise and general tasks. Offers a good balance between comfort, freedom of movement and hand protection. With Ansell zonz® Comfort Fit Technology™ to reduce hand fatigue. Öko-Tex® Standard 100.

With Nylon-Spandex material and silicone-free coating. free of latex.

Standard:

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Oil grip	good
DMF-free	no
Accuracy of fit	very good
Heat protection	not available

Breathability	very good
Glove size	10
Wet grip	medium
silicone-free	no
Material of coating	Nitrile
Touch sensitivity	very good
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	DMF-free
Glove characteristics	free of latex
EN 388	3131A
Backing material	Spandex nylon
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Length	192 mm
Colour	black / grey
Weight	20,4 g
Knitted technology	15G
Application	reusable
Material	Nitrile foam
Cut protection class	A
Type of product	Multi-purpose gloves

