

**Table trolley with 2 platforms up to 1200 kg, Type: 12405****Order data**

Order number	919865 12405
GTIN	4017976124056
Item class	96F

Description**Version:**

Welded steel and sections and tubes, platforms made of non-slip platform of marine plywood. 2 fixed wheels and 2 castors (with parking brake), high-grade resilient solid blue-grey rubber treadless tyres (200x50 mm), and hubs with roller bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Platform area width	1600 mm
Platform area depth	800 mm
Height of bottom shelf	283 mm
Width	1810 mm
Number of castors with parking brake	2
Material of wheel	Resilient solid rubber

Weight	100 kg
Number of fixed wheels without parking brake	2
Height	925 mm
Height of top shelf	925 mm
Type	12405
Standard	EN 1757-3
Wheel Ø	200 mm
Depth	800 mm
maximum load capacity	1200 kg
Load capacity of top shelf	500 kg
Type of product	Table trolleys