

**Table trolley with 3 platforms, Type: 4832****Order data**

Order number	919875 4832
GTIN	4017976048321
Item class	96F

Description**Version:**

Welded steel construction, 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Oil-tight trays with **40 mm** high edge, 3 shelves.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Type	4832
Material of wheel	TPE
Height of middle shelf	560 mm

Load capacity of top shelf	200 kg
maximum load capacity	400 kg
Load capacity of middle shelf	200 kg
Platform area width	1000 mm
Weight	61 kg
Width	1171 mm
Height	910 mm
Height of bottom shelf	248 mm
Wheel Ø	200 mm
Height of top shelf	870 mm
Standard	EN 1757-3
Platform area depth	700 mm
Depth	700 mm
Type of product	Table trolleys