

**Trolley with handle, Type: KF33****Order data**

Order number	919805 KF33
GTIN	4017976011646
Item class	96F

Description**Version:**

Welded steel tubes, platform made of chipboard.

2 fixed wheels and 2 castors (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Width	860 mm
Height	875 mm
Weight	19 kg
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2

Height of bottom shelf	195 mm
Material of wheel	TPE
Height of top shelf	770 mm
Type	KF33
Wheel Ø	125 mm
Platform area width	600 mm
Safe working load	250 kg
Standard	EN 1757-3
Platform area depth	450 mm
Depth	450 mm
Load capacity of top shelf	100 kg
Type of product	Trolley with handle