



## Round sheet metal punch set "Metric" Ø 12.5 – 63.5 mm in a sheet metal case



### Order data

Order number	834550
GTIN	2050001002846
Item class	86C

### Description

#### Supplied with:

1 each matrix punch and matrix (like round sheet metal punch No. 834000) for hole Ø 12.5 (M12×1.5); 16.5 (M16×1.5); 20.5 (M20×1.5); 25.5 (M25×1.5); 32.5 (M32×1.5); 40.5 (M40×1.5); 50.5 (M50×1.5); 63.5 (M63×1.5).

1 draw bolt (No. 834040 size 16/70).

4 ball thrust bearing draw bolts (No. 834060 size 10/55; 16/70; 20/90 and No. 834040 size 6/30 with ball thrust bearing).

1 step drill similar to No. 118320 (= Ø 7 - 21 mm).

1 sheet metal case size 335×230×55 mm.

### Technical description

Type of product	Punching tool
-----------------	---------------

### Accessories

Spare ball bearing draw bolt for round sheet metal punches Thread Ø / Length 10/55 mm	834060 10/55
---	--------------

Round sheet metal punch without ball thrust bearing Punch Ø (hole Ø) 63,5 mm	834000 63,5
Spare ball bearing draw bolt for round sheet metal punches Thread Ø / Length 20/90 mm	834060 20/90
Spare ball bearing draw bolt for round sheet metal punches Thread Ø / Length 16/70 mm	834060 16/70
Spare draw bolt for round sheet metal punches Thread Ø / Length 6/30 mm	834040 6/30
Round sheet metal punch without ball thrust bearing Punch Ø (hole Ø) 12,5 mm	834000 12,5
Round sheet metal punch without ball thrust bearing Punch Ø (hole Ø) 25,5 mm	834000 25,5
Spare draw bolt for round sheet metal punches Thread Ø / Length 16/70 mm	834040 16/70