



LED rechargeable pencil work light, Type: MAGPEN3



Order data

Order number	081517 MAGPEN3
GTIN	5708997351161
Item class	08C

Description

Version:

LED cordless work lamp with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. Steplessly dimmable.

Powerful general-purpose LED **rechargeable battery** torch with side main beam and torch head spotlight. With pocket clip and integral magnet.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Supplied with:

Supplied with USB charging cable.

IP Index of Protection: IP 20

ATEX zone: no

Illumination: 15 - 150 lm

Working life: 2 - 20 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Overall length: 174 mm

Technical description

Manufacturer's designation	MAG PEN3
Battery voltage	3.7 V
Working life	2 - 20 h
ATEX zone	no
Illumination	15 - 150 lm
Weight	98 g
Battery capacity	0.75 A·h
IP Index of Protection	IP 20
Number of rechargeable batteries contained	1
Overall length	174 mm
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Flashlight

Accessories

USB charger Cables + adapters Type CABLE	081512 CABLE
--	--------------